

TECHSPEC®

25mm VIS, 50R/50T, Non-Polarizing In-Line Cube Beamsplitter



Stock #20-096

10 TO 12 DAYS

-

1

+

₹25,230.00

ADD TO CART

Qty 1-5
₹25,230.00
Qty 6+
₹21,663.00
Volume Pricing
Request Quote

Get Product Downloads



Beam Deviation (arcmin):
≤2

Bevel:
Protective bevel as needed

Clear Aperture (%):
>90

Coating:

MS
Coating Specification: R _{avg} <0.5% @ 430 - 670nm
Construction: Cube
Dimensions (mm): 25.0 x 25.0 x 25.0
Note: Absorptive Surface Treatment on Blackened Face
Reflection/Transmission Ratio (R/T): 50/50
Substrate: ☐ N-BK7
Surface Quality: 40-20
Type: Non-Polarizing Beamsplitter
Wavelength Range (nm): 430 - 670
[Ts-Tp]: <6%
Absolute Transmission (%): 45 ±10
Average Transmission (%): 45 ±5
Power (fringes) @ 632.8nm: 1.25
Irregularity (fringes) @ 632.8nm: 0.25

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View