

## 25mm x 25mm 220 Grit Ground Glass Diffuser



Stock **#45-654** **20+ In Stock**

- 1 + MRP ₹2,421

**i** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-10	₹2,421 each
Qty 11+	₹2,144 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Ground Glass Diffuser **Type:**  
Sandblasted on first surface **Note:**

### Physical & Mechanical Properties

±0.76 **Dimensional Tolerance (mm):**

**Dimensions (mm):**

25.00 x25.00

Cut **Edges:**

220 **Grit:**

1.60 **Thickness (mm):**

25.00 **Width (mm):**

25.00 **Length (mm):**

## Optical Properties

Uncoated **Coating:**

Float Glass **Substrate:**

350 - 2000 **Wavelength Range (nm):**

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

**Reach 247:**  
[Compliant](#)

**Country of Origin:**  
United States

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91-80-6845 0000


## Product Details

- Available in Sizes Ranging from 5mm Diameter to 250mm Square
- Low Scatter Loss
- Evenly Ground Surface for Even Diffusion
- [Fused Silica Substrates](#) Available

Ground Glass Diffusers are comprised of high tolerance, quality ground glass making them ideal for a variety of industrial applications. The float glass substrate has excellent visible transmission and is ideal for general diffusing applications. A 120-grit, 220-grit or 600-grit (as noted) sandblast is used to create a diffuse surface on the glass. Ground Glass Diffusers have even diffusion across the entire surface from undergoing two orthogonal passes during this sandblast process. The scattering is a compromise of low scatter loss and medium diffusion. Typical applications include use in screens, illuminator diffusion, and targets.

Can't find what you need? Get a quick [custom quote](#).

## Technical Information



[Quote Your Size](#)

[Compatible Mounts](#)