

25mW, 405nm Violet Alignment Laser Diode Module



Violet Alignment Laser Diode

Stock #19-461

10 TO 12 DAYS

-

1

+

₹40,890.00

ADD TO CART

Qty 1-9
₹40,890.00
Qty 10+
₹36,801.00
Volume Pricing
Request Quote

Get Product Downloads



Operating Temperature (°C):

-10 to 50

Operating Voltage (V):

5

Output Power (mW):

25

Wavelength (nm):

405.00
Wavelength Tolerance (nm): ±5
Power Supply: Power Supply Required and Sold Separately. USA: #83-855 Europe: #83-855 Japan: #13-640 Korea: #33-770 China: #83-855
Modulation Frequency (kHz): 0 - 10
Beam Diameter (mm): 3.5 typical
Beam Divergence (mrad): <0.5
Laser Class - CDRH: IIIb
Color: Violet
Length (mm): 36.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant