

TECHSPEC[®] 2.5" Dia. x 25" FL Uncoated, Spherical Mirror



Stock #32-081 CLEARANCE 10 TO 12 DAYS

-

1

+

₹13,567.65

ADD TO CART

Qty 1+
₹13,567.65

Volume Pricing
Request Quote

Get Product Downloads



Substrate:

BOROFLOAT[®]

Focal Length Tolerance (%):
±2

Surface Quality:
60-40

Surface Accuracy:
λ/8

Diameter (inches):
2.5

Diameter (mm): 63.50 +1.0/-0
Diameter Tolerance (inches): +0.04/-0
Effective Focal Length EFL (inches): 25.0
Effective Focal Length EFL (mm): 635.00
Radius of Curvature (mm): 1,270.00
Aperture (f/#): f/10
Coating: Uncoated
Coating Type: Uncoated
Back Surface: Ground
Edge Thickness ET (inches): 0.38
Edge Thickness ET (mm): 9.65
Edge Thickness Tolerance (%): +0.0/-10
Type: Spherical Mirror

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View