

25X Peak Direct Measuring Microscope



Peak Direct Measuring Microscopes

Stock **#39-110** **3 In Stock**

-

1

+

₹26,190

ADD TO CART

Volume Pricing	
Qty 1-4	₹26,190 each
Qty 5+	₹24,840 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties	
3.30	Field of View (mm):
At Focus: 41.5 Dia. x 122 L	Dimensions (mm):
0.05	Graduation (mm):
0 - 3.0	Reticle Scale (mm):

Up to 22		Depth Measurements (mm):
Optical Properties		
25X		Magnification:
17.0		Working Distance (mm):
Regulatory Compliance		
View		Certificate of Conformance:
Japan		Country of Origin:
Edmund Optics India Private Limited		Imported By:

Product Details

Reticle should not be removed or replaced.

- Multiple Magnification Options
- Illuminated Models Available with English or Metric Reticles
- Removable Clear Acrylic Base

Peak Direct Measuring Microscopes are high power, portable microscopes designed for precise depth measurements. Peak Direct Measuring Microscopes feature a 10X focusable eyepiece and a scale with an accuracy of 0.1mm for measuring the length, width, or depth of an object. The clear cutaway acrylic base allows for manipulation of the sample while viewing. Illuminated models feature a removable pen illuminator, and include two AA batteries. Peak Direct Measuring Microscopes are sold with a hard-shell vinyl storage case.

Note: Reticle should not be removed or replaced.