

26 x 62mm FL, Grade 1, Double-Convex Lens



Stock **#76-092** CLEARANCE CONTACT US

-

1

+

₹866

ADD TO CART

Volume Pricing	
Qty 1+	₹866 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

Physical & Mechanical Properties

Diameter (mm):

26.00

Optical Properties

Effective Focal Length EFL (mm):

62.00

Regulatory Compliance

[View](#)

Certificate of Conformance:

PRODUCT DETAILS

- Ideal for Experimenting and Prototyping Applications
- Quantities Extremely Limited, Buy While Supplies Last
- For Even More Deals, Check out [Mega Clearance: Optics](#)

Double-convex (DCX) lenses have two outward curved surfaces, a positive focal length and are useful for 1:1 imaging and in multi-element systems.

20 - 29.9mm Experimental Quality Double-Convex (DCX) Lenses are offered in several experimental grade options. Grade 1 is standard optical glass, edged, free of visible scratches, chips, stains, or oxidation. Grade 2 is unedged, non-optical glass, small chips, slight stains, or other defects. They may have slight edge cement separation.

Note: Specifications for experimental grade optics may vary as much as 10% from those listed. Also, no additional information is available other than what is provided.

TECHNICAL INFORMATION

