

2.62", English Rotary Stage



Stock #38-193 **2 In Stock**

-

1

+

₹86,553

ADD TO CART

Volume Pricing	
Qty 1+	₹86,553 each
Need More?	Request Quote

Product Downloads

General

Type:

English

Physical & Mechanical Properties

Weight (lbs):

1.8

Stage Size (mm):

66.5 x 66.5

Stage Size (inches):

2.62 x 2.62

Construction:

Aluminum top and base; steel tangent arm drive	
0.50" Dia. Thru	Center Hole:
±5 (Fine), 360 (Coarse)	Travel (°):
Increments (arcmin):	
12	
Load Capacity, Normal (lbs):	
10	
Load Capacity, Vertical (lbs):	
4	
Type of Movement:	
Rotary	
Guide System:	
Ball Bearing	
Table Diameter (inches):	
2.62	

Hardware & Interface Connectivity

Type of Drive:	
Tangent Arm	

Threading & Mounting

Mounting Threads:	
(4) 6-32 on 1.125" dia. B.C., (4) 1/4-20 on 2.00" dia. B.C.	

Regulatory Compliance

RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
Country of Origin:	
United States	
Imported By:	
Edmund Optics India Private Limited	

Product Details

- Low Wear, Low Friction Movement with Coarse or Fine Adjustment
- 2 or 2.62" Diameter Stages with Tapped Mounting Holes
- Calibrated Dial with 12 Minute Vernier for Accurate Read-Out

Compact miniature stages provide low-friction rotary movement with both coarse and fine adjustment. This allows for quick rotation over a continuous 360° travel, plus precise angular adjustment at any selected position. Features include preloaded angular contact ball bearing system, a positive position lock, a 2.00" or 2.62" diameter stage with tapped mounting holes and a calibrated dial with six minute vernier for accurate positional read-out. It can be combined with our compatible linear translation stages for multi-axis linear-rotary applications.

Technical Information

