

[See all 32 Products in Family](#)

266nm, 4-6mm Dia. Input Beam, Focal Flat Top Beam Shaper | Focal- π Shaper_266_Q-5

See More by [AdlOptica](#)



#25-842: 266nm, 4-6mm Dia. Input Beam, Focal Flat Top Beam Shaper | Focal- π Shaper_266_Q-5



Stock **#25-842** 1 In Stock

-

1

+

₹2,96,550

ADD TO CART

Volume Pricing	
Qty 1-4	₹2,96,550 each
Qty 5+	₹2,64,150 each
Need More?	Request Quote

Product Downloads

General	
Focal- π Shaper_266_Q-5	Model Number:
Beam Shaper	Type:
#12-322	Compatible Adapter:

Physical & Mechanical Properties	
29.00	Length (mm):
50	Weight (g):
20	Clear Aperture CA (mm):
42.00	Diameter (mm):
4 - 6	Input Beam Diameter, 1/e ² (mm):
Optical Properties	
>99	Transmission (%):
266	Design Wavelength DWL (nm):
250 - 275	Wavelength Range (nm):
TEM ₀₀	Input Beam Mode:
<1.5	Typical Input Beam Mode Quality, M ² :
±20	Input Beam Divergence (mrad):
Electrical	
0.2	Maximum Input Power, CW (kW):
Threading & Mounting	
M30 x0.75	Inner Thread:
M30 x0.75	Outer Thread:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 250:
Germany	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Shapes Gaussian Beams to Airy Disk Profile
 - Airy Disk is Focusable to Flat Top Spot
 - Near 100% Efficiency
 - [AdlOptica πShaper Flat Top Beam Shapers](#) Also Available
- AdlOptica Focal-πShaper (piShaper) Q Flat Top Beam Shapers are used to transform Gaussian beams to flat-top profiles after focusing through a lens. This is accomplished by transforming the Gaussian beam to airy disk profiles immediately after the piShaper. These beam shapers feature a compact design with inner and outer threading, making them easy to integrate into equipment. AdlOptica Focal-πShapers are advantageous for beam shaping in micromachining applications, including scribing and PCB drilling, as well as micro-welding applications. Multiple models are available at Nd:YAG, Ti:Sapphire, and Infrared wavelengths with compatible input beam diameters as small as 2.5mm and up to 23mm.

Technical Information

