

TECHSPEC® 2" Dia, 20" FL Uncoated, Spherical Mirror



Stock #32-820 10 TO 12 DAYS

- 1 + **₹10,440.00**

ADD TO CART

Qty 1-9
₹10,440.00
Qty 10+
₹8,874.00
Volume Pricing
Request Quote

Get Product Downloads



Substrate: BOROFLOAT®

Focal Length Tolerance (%):
±2

Surface Quality:
60-40

Surface Accuracy:

N4
Diameter (inches): 2.0
Diameter (mm): 50.80 +0.5/-0
Diameter Tolerance (inches): +0.02/-0
Effective Focal Length EFL (inches): 20.00
Effective Focal Length EFL (mm): 508.00
Radius of Curvature (mm): 1,016.00
Aperture (f/#): f/10
Coating: Uncoated
Coating Type: Uncoated
Back Surface: Ground
Edge Thickness ET (inches): 0.50
Edge Thickness ET (mm): 12.70
Edge Thickness Tolerance (%): +0.0/-15
Type: Spherical Mirror

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View