

TECHSPEC[®] 2" Dia. Enhanced Aluminum, λ /10 Flat Fused Silica



Stock #01-914-533 10 TO 12 DAYS

-

1

+

₹22,098.00

ADD TO CART

Qty 1-10
₹22,098.00
Qty 11+
₹19,923.00
Volume Pricing
Request Quote

Get Product Downloads



Surface Flatness (P-V):
 λ /10 (measured before coating)

Back Surface:
Commercial Polish

Surface Quality: 60-40
Diameter (mm): 50.80 +0.0/-1.0
Substrate: ☐ Fused Silica (Corning 7980)
Coating Specification: R _{avg} >95% @450 - 650nm
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Clear Aperture CA (mm): 45.72
Note: Flatness is specified as Peak to Valley
Thickness (mm): 12.70 ±1.5
Thickness Tolerance (mm): ±1.5
Type: Flat Mirror
Wavelength Range (µm): 0.45 - 0.65
Wavelength Range (nm): 450 - 650
Damage Threshold, Reference: ☐ 0.2 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant