

## 2" x 2" (1000 lp/inch), Ronchi Ruling



Stock #56-613 10 TO 12 DAYS

- 1 +

₹33,408.00

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-4                       |
| ₹33,408.00                    |
| Qty 5+                        |
| ₹31,816.00                    |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

### Get Product Downloads

**Coating:**  
Vacuum Deposited Chrome, OD >3.0

**Dimensional Tolerance (inches):**  
±0.02

**Substrate:**  
Float Glass

**Optical Density OD (Average):**  
3.00

|                                                            |
|------------------------------------------------------------|
| <div>Dimensions (inches):<br/>2 x2</div>                   |
| <div>Surface Quality:<br/>60-40</div>                      |
| <div>Thickness (mm):<br/>1.50</div>                        |
| <div>Type:<br/>English</div>                               |
| <div>Parallelism (arcmin):<br/>±60</div>                   |
| <div>Dimensional Tolerance (mm):<br/>± 0.02</div>          |
| <div>Frequency (lp/inch):<br/>1000.00</div>                |
| <div>Line to Line Parallelism (arcsec):<br/>≤2</div>       |
| <div>Parallelism of Pattern to Substrate (°):<br/>±1</div> |
| <div>Surface Flatness (P-V):<br/>1λ</div>                  |

### Regulatory Compliance

|                                                                 |
|-----------------------------------------------------------------|
| <div>RoHS 2015:<br/><a href="#">Compliant</a></div>             |
| <div>Reach 209:<br/><a href="#">Compliant</a></div>             |
| <div>Certificate of Conformance:<br/><a href="#">View</a></div> |

---