

2" x 2" (750 lp/inch), Ronchi Ruling



Stock #56-612 10 TO 12 DAYS

- 1 +

₹30,102.00

ADD TO CART

Qty 1-4
₹30,102.00

Qty 5+
₹28,684.00

Volume Pricing
Request Quote

Get Product Downloads

Coating:
Vacuum Deposited Chrome, OD >3.0

Dimensional Tolerance (inches):
±0.02

Substrate:
Float Glass

Optical Density OD (Average):
3.00

Dimensions (inches): 2 x2
Surface Quality: 60-40
Thickness (mm): 1.50
Type: English
Parallelism (arcmin): ±60
Dimensional Tolerance (mm): ± 0.02
Frequency (lp/inch): 750.00
Line to Line Parallelism (arcsec): ≤2
Parallelism of Pattern to Substrate (°): ±1
Surface Flatness (P-V): 1λ

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View
