

[All Products](#) / [Microscopy](#) / [Finite Conjugate Objectives](#) / [Mitutoyo Compact Objectives](#)

[See all 3 Products in Family](#)

2X Mitutoyo Compact Objective

See More by [Mitutoyo](#)



Mitutoyo Compact Objectives



Stock **#56-989** 10 TO 12 DAYS

- 1 +

₹40,020.00

ADD TO CART

Qty 1+
₹40,020.00

Volume Pricing
Request Quote

Get Product Downloads

Effective Focal Length EFL (mm):
60.19

Horizontal Field of View, 1/2" Sensor:
3.20mm

Horizontal Field of View, 2/3" Sensor:
4.40mm

Focal Length FL (mm):

60.33
Model Number: 375-032
Length (mm): 18.00
Length excluding Threads (mm): 18.00
Magnification: 2X
Maximum Diameter (mm): 30
Maximum Sensor Format: 2/3"
Numerical Aperture NA: 0.06
Mounting Threads: M26 x 36 TPI
Type: Microscope Objective
Resolving Power (µm): 4.6
Depth of Field (µm): 76.00
Field of View, 24 Diameter Field Eyepiece (mm): 12.0
Field of View, 18 Diameter Field Eyepiece (mm): 9.0
Operating Temperature (°C): +5 to +35
Operating Humidity: 65±20%
Working Distance (mm): 92.0
Weight (g): 35.00
Wavelength Range (nm): 435 - 655
Style: Finite Conjugate
Manufacturer: Mtutoyo
Field Number (mm): 24
Parfocal Length (mm): 110
Immersion Liquid: N/A

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant