


TECHSPEC®

3" Dia. λ /10 Fused Silica Dual Surface Flat



Stock #43-428

10 TO 12 DAYS

-

1

+

₹61,335.00

ADD TO CART

Qty 1+
₹61,335.00
Volume Pricing
Request Quote

Get Product Downloads

Surface Flatness (P-V):

λ /10

Abbe Number (v_d):

67.8

Coating:

Uncoated

Coefficient of Thermal Expansion CTE ($10^{-6}/^{\circ}\text{C}$):

0.52 (+5 to +35°C)

0.57 (0 to +200°C)

0.48 (-100 to +200°C)
Diameter (mm): 76.20 ±1.0
Thickness (mm): 19.05 ±1.5
Diameter (inches): 3.00 ±0.04
Thickness (inches): 0.75 ±0.06
Clear Aperture CA (mm): 68.60
Construction: Dual Surface
Density (g/cm³): 2.20
Index of Refraction n_d: 1.458
Knoop Hardness (kg/mm²): 522
Parallelism (arcmin): <3
Poisson's Ratio: 0.16
Substrate: Fused Silica
Surface Quality: 60-40
Type: Interferometry Window
Wavelength Range (nm): 200 - 2200
Young's Modulus (GPa): 73
Bevel: Protective as needed

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View