

3" LED Ring Light 660nm with Barrel Mount

See More by [Advanced Illumination](#)



Stock #66-777 [CONTACT US](#)

-

1

+

₹49,764.00

ADD TO CART

Qty 1+
₹49,764.00
Volume Pricing
Request Quote

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:	Red
Diameter (mm):	85.00
Height (mm):	35
Inner Diameter (mm):	55.4

Model Number: RL1424B-660-IC
Mount: Barrel Mount
Operating Temperature (°C): 0 to 65
Dimensions (mm): 85 Dia x 35 T
Mounting Threads: M4 x4
Wavelength (nm): 660.00
Working Distance (inches): 4.00
LED Lifetime (hours): 50,000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Light Distribution (%): ±10 edge to edge (dependent on working distance)
Number of LEDs: 24.00
Number of Channels: 1.00
Field Coverage (mm): 43.18 (1.7 inches)
Maximum Trigger Frequency (Hz): 30.00
Type of Illumination: LED Illuminator
Note: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Manufacturer: Advanced Illumination
Geometry: Ring Light
Illumination Mode: Constant

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Contains SVHC(s)