

[See all 62 Products in Family](#)

Coherent® StingRay™ Projection Head 1265421 | 640nm, 5mW, 30° Fan

See More by [Coherent®](#)



Stock #89-575 1 In Stock

-

 1

+

 ₹30,015

ADD TO CART

Volume Pricing	
Qty 1+	₹30,015 each
Need More?	Request Quote

Product Downloads



General

Type:	
1 Line	
Compatible Laser Models:	
86-849	
Manufacturer:	
Coherent®	

Optical Properties

640.00	Wavelength (nm):
Red	Color:
30.00	Fan Angle (°):
Electrical	
5.00	Maximum Power (mW):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Singapore	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- External Focus with up to 100mW Output Power
- Auto Scaling Input Power 5 - 24VDC with Reverse Polarity Protection
- Built-In Microcontroller for Fault Monitor
- **Coherent® StingRay™ Developer's Kit** also available

Coherent® StingRay™ and BioRay™ Laser Diode Modules are ideal for a variety of alignment, machine vision, and biomedical applications. They are available in a wide range of output powers , wavelengths, and fan angles. High precision optical components and sophisticated drive electronics provide power and control to your application, reducing signal-to-noise ratios and increasing measurement speed. Coherent® StingRay™ and BioRay™ Laser Diode Modules are designed with a flat top power distribution across the beam profile for consistency in line projection widths.

Note: For CDRH certified systems (Class IIIb), **#86-878** Laser Controller and additional external voltage source (0.5–5V) with BNC connector is required.