

Richardson Gratings™ 300 Grooves, 25 x 25mm, 1700nm, Plane Ruled Reflection Grating

See More by [Richardson Gratings™](#)



Richardson Gratings™ High Precision Plane Ruled Reflective Diffraction Gratings



Stock **#37-131** 10 TO 12 DAYS

-

1

+

₹14,616.00

ADD TO CART

Qty 1+
₹14,616.00

Volume Pricing
Request Quote

Get Product Downloads



Groove Density (grooves/mm):
300

Wavelength Range (nm):
700 - 1000

Blaze Wavelength (nm):
1700 ±25

Blaze Angle (°): 14.6
Peak Efficiency, Typical (%): 86
Dimensions (mm): 25.0 x 25.0 ±0.1
Clear Aperture (%): >90
Coating: Aluminium
Construction: Ruled Grating
Length (mm): 25.00
Substrate: ☐ Float Glass
Thickness (mm): 6.00 ±0.5
Type: Reflective Diffraction Grating
Width (mm): 25.00
Reflected Wavefront, RMS: λ/4
Centering of Ruled Area on Substrate (mm): ±1
Alignment of Grooves to Edge (°): ±0.15
Groove Spacing Tolerance (%): <0.05
Polarization: Unpolarized
Master Reference: 0891
Spectral Order (m): 1

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View