

[See all 72 Products in Family](#)

**TECHSPEC® 300 x 300mm Linear Polarizing Film (XP42-40)**



Stock #29-497 **9 In Stock**

MRP ₹20,481

**i** Price inclusive of all taxes

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | ₹20,481 each                  |
| Qty 11-25      | ₹17,555 each                  |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

**General**

Linear Polarizer **Type:**

**Note:**  
Polarization axis is parallel to marking on protective film.

**Physical & Mechanical Properties**

300.0 x 300.0 ±3.0 **Dimensions (mm):**

0.40 ±0.05 **Thickness (mm):**

Polarizing Film **Construction:**

## Optical Properties

Uncoated, Protective Film on Both Sides **Coating:**

9000:1 (nominal at 555nm) **Extinction Ratio:**

[Polymer Film XP42-40](#) **Substrate:** □

Single: 42 ±2  
Parallel: 36.4  
Crossed: <0.004 (nominal at 555nm) **Transmission (%):**

400 - 700 **Wavelength Range (nm):**

>99.98 (nominal at 555nm) **Polarization Efficiency (%):**

42 ±2 **Transmission, Single (%):**

36.4 **Transmission, Parallel (%):**

<0.004 (nominal at 555nm) **Transmission, Crossed (%):**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 235:**

Japan **Country of Origin:**

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91-80-6845 0000 **Imported By:**

## Product Details

- High Transmission of Unpolarized Light from 400 – 700nm
- Excellent Extinction Ratio of 9000:1
- Available in Custom Sizes
- [High-Temperature](#) Options Also Available


Ideal for a range of imaging applications, TECHSPEC® High Contrast Linear Polarizing Film (XP42) features an excellent extinction ratio and high transmission from 400 – 700nm. This polarizing film is offered in multiple thicknesses; thicker polarizing film has increased rigidity. Available in sheets, TECHSPEC® High Contrast Linear Polarizing Film (XP42) can be cut to fit any application need.

**Note:** Polarizer Film with adhesive available.

### Immediate Custom Quotes Available

If you have a need for any round, square, or rectangular size of a TECHSPEC High Contrast Linear Polarizing Film (XP42) in dimensions between 3mm and 600mm, please visit our [Polarizing Film Tool](#). We'll provide an immediate quote, and can deliver the part to your requested size in approximately 3 weeks. A full list of standard manufacturing tolerances and restrictions are listed. For fully customized polymer polarizers to your requirements, visit our [Customized Polymer Polarizers Capabilities](#) page.

## Technical Information



XP42 – Linear Polarizer



XP44 – Linear Polarizer

