

300 x 300mm Right-Handed Plastic Circular Polarizer (CP42HER)



Stock #14-357 CLEARANCE 10 TO 12 DAYS

-

1

+

₹23,316.00

ADD TO CART

Qty 1-10
₹23,316.00
Qty 11+
₹21,141.00
Volume Pricing
Request Quote

Get Product Downloads

Substrate: [Polymer Film CP42HER](#)

Length (mm):
300.00

Operating Temperature (°C):
-40 to +80

Dimensions (mm):
300.0 x 300.0

Thickness (mm): 0.27 ±0.04
Thickness Tolerance (mm): ±0.03
Transmission (%): 42
Type: Right-Handed Circular Polarizer
Dimensional Tolerance (mm): +0.0/-3.0
Construction: Polarizing Film
Wavelength Range (nm): 400 - 700
Polarization Efficiency (%): >99.90
Width (mm): 300.00
#Sorting: 33.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Contains SVHC(s)