

225mm Max. Aperture, Iris Diaphragm



Stock **#70-895** 10 TO 12 DAYS

⊖ 1 ⊕

₹67,164.00

ADD TO CART

Qty 1-4
₹67,164.00
Qty 5+
₹59,369.00
Volume Pricing
Request Quote

Get Product Downloads

Type: Unmounted
Minimum Aperture (mm): 12.0
Maximum Aperture (mm): 225.0
Outer Diameter (mm): 300.0

Construction: Aluminum Housing, Blue Tempered Spring Steel Leaves
Lever Diameter (mm): 5.00
Lever Length (mm): 40.50
Number of Leaves: 18.00
Thickness (mm): 19.00

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)