


3000μm, Optical Grade Plastic Optical Fiber Unjacketed



Stock **#53-833** [CONTACT US](#)

-

1

+

₹400.00

ADD TO CART

Qty 1+
₹400.00

Volume Pricing
Request Quote

Get Product Downloads

Acceptance Angle (°):
60.00

Minimum Bend Radius (mm):
75.00

Substrate: ☐
Acrylic

Attenuation (dB/m):
0.20

Numerical Aperture NA:
0.50

Number of Fibers: 1.00
Operating Temperature (°C): -55 to +70
Outer Diameter (mm): 3.0
Core Diameter (µm): 2950.00
Fiber Diameter (µm): 3000.00
Length (ft): Cut to Order, Minimum 10
Construction: Unjacketed
Index of Refraction n_d - Core: 1.49
Index of Refraction n_d - Cladding: 1.402
Attenuation (dB/km): 150 - 300 (@ 650nm)
Numerical Aperture (NA) Tolerance: ±0.03
Diameter Tolerance (%): ±6

Regulatory Compliance

RoHS 2015: Compliant
Reach 197: Compliant
Certificate of Conformance: View