

TECHSPEC® 30.0mm Dia. x 120.0mm FL, Uncoated, Plano-Convex Lens



Stock **#45-243** 10 TO 12 DAYS
[Other Coating Options](#)

- 1 + **₹3,089.00**

ADD TO CART

Qty 1-9
₹3,089.00
Qty 10+
₹2,784.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
30.00 +0.0/-0.025

Effective Focal Length EFL (mm):
120.00 @587.6nm

Back Focal Length BFL (mm): 116.04
Coating: Uncoated
Substrate:  N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 6.00 ±0.10
Edge Thickness ET (mm): 4.16
Radius R₁ (mm): 62.02
Clear Aperture CA (mm): 29
f#: 4
Numerical Aperture NA: 0.13
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 2200

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View
