

TECHSPEC[®] 30.0mm Dia. x 30.0mm FL, VIS-EXT, Inked, Plano-Convex Lens



Stock #88-745-INK [CONTACT US](#)

[Other Coating Options](#)

-

1

+

₹5,742.00

ADD TO CART

Qty 1-9
₹5,742.00
Qty 10+
₹5,177.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
30.00 ±0.025

Effective Focal Length EFL (mm):
30.00 @ 587.6nm

Back Focal Length BFL (mm): 26.13
Coating: VIS-EXT (350-700nm)
Coating Specification: R _{avg} <0.5% @ 350 - 700nm
Substrate: ☐ N-SF11
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 6.90 ±0.10
Edge Thickness ET (mm): 1.50
Radius R₁ (mm): 23.54
Clear Aperture CA (mm): 29
f#: 1
Numerical Aperture NA: 0.50
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 700
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View