

300mm Dia x 800mm FL Alum. Coated, Ellipsoidal Reflector



Precision Ellipsoidal Reflectors

Stock #90-972 10 TO 12 DAYS

- 1 +

₹108,054.00

ADD TO CART

Qty 1-10
₹108,054.00
Qty 11+
₹95,396.00
Volume Pricing
Request Quote

Get Product Downloads

Substrate: BOROFLOAT®

Coating:
Protected Aluminum (400-700nm)

Coating Specification:
Ravg >85% @400 - 700nm

Coating Type:

Metal
Center Hole Diameter (mm): 80.0
Height (mm): 147.0 ±0.5
Inner Diameter (mm): 290
Outer Diameter (mm): 300.00 +0.0/-0.5
Type: Specialty Mirror
Wavelength Range (nm): 400 - 700
Distance to Focal Point f₁ (mm) : 45 ±10
Distance to Focal Point f₂ (mm): 790 ±10

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View