

[See all 17 Products in Family](#)

**TECHSPEC® 30.8mm Motorizable Iris Spur Gear**



30.8mm Motorizable Iris Spur Gear, #34-519

Stock **#34-519** **20+ In Stock**

- 1 + MRP ₹2,095

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-4	₹2,095 each
Qty 5-9	₹1,847 each
Qty 10-25	₹1,725 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**Physical & Mechanical Properties**

30.8	<b>Outer Diameter (mm):</b>
Brass	<b>Construction:</b>
30	<b>Pitch Diameter (mm):</b>

## Regulatory Compliance

**Exempt** RoHS 2015:

**View** Certificate of Conformance:

**Contains SVHC(s)** Reach 247:

**Country of Origin:**  
Germany

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91-80-6845 0000

## Product Details

- Fast Accurate Repeatable Motion
- Dual Control Gear and Lever Mechanics
- Removable Pin for OEM Integration
- Anti-Reflection (AR) Leaves Available
- Iris Diaphragm Mounts and Motor Sold Separately

TECHSPEC® High Performance Motorizable Irises are designed for integration into custom applications and for use in a lab environment. These irises include two methods for controlling the aperture size: one by a standard pin which enables standard angular deviation and the other that duplicates the movement of the pin by replicating the teeth of a spur gear on the inner housing of the iris. This feature allows for custom motion control in conjunction with a compatible spur gear. TECHSPEC® High Performance Motorizable Irises maintain fast, accurate, and repeatable movement to any location through the iris's range of motion. The 7mm, 12mm, 22mm, 28mm, and 34mm Max Aperture configurations are also available with Anti-Reflection (AR) Leaves.

## Technical Information

