

30° Diffusing Angle 25mm Dia., Fused Silica Holographic Diffuser



Holographic UV Diffusers

Stock **#48-510** 10 TO 12 DAYS

-

1

+

₹39,803.00

ADD TO CART

Qty 1+
₹39,803.00

Volume Pricing
Request Quote

Get Product Downloads

Angle Tolerance (°): ±3
Diffusing Angle (°): 30 (FWHM)
Clear Aperture CA (mm): 21.6 ±0.1
Diameter (mm): 25.00 ±0.1
Operating Temperature (°C): -40 to +170

Substrate: 
[Fused Silica](#) (Corning 7980)

Transmission (%):
Typical: 90

Type:
Holographic Diffuser

Wavelength Range (nm):
400 - 700

Construction:
Mounted

Mount Thickness (mm):
4.7 ±0.1

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 233:
[Compliant](#)