

30mm Dia. 1000-2000nm, NIR Linear Polarizer



Stock **#48-889** [CONTACT US](#)

-

1

+

₹32,190.00

ADD TO CART

Qty 1-5
₹32,190.00
Qty 6+
₹27,318.00
Volume Pricing
Request Quote

Get Product Downloads



Coating:
Uncoated

Diameter (mm):
30.00

Extinction Ratio:
1000:1

Substrate: ☐

Polymer Film on B270
Operating Temperature (°C): -25 to +80
Thickness (mm): 2.00
Thickness Tolerance (mm): ±0.2
Transmission (%): 33.00
Transmission Tolerance (%): ±3
Type: Linear Polarizer
Parallelism (arcmin): <4
Dimensional Tolerance (mm): +0.0/-0.2
Construction: Dichroic Polarizing Film on Glass
Wavelength Range (nm): 1000 - 2000

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View