

TECHSPEC[®] 30mm Dia. Protected Gold, λ/4 Mirror



Stock #63-176 10 TO 12 DAYS

-

1

+

₹9,135.00

ADD TO CART

Qty 1-5
₹9,135.00
Qty 6+
₹7,308.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
30.00

Surface Flatness (P-V):
λ/4

Substrate: ☐
[BOROFLOAT[®]](#)

Back Surface:

Commercial Polish
Surface Quality: 60-40
Dimensional Tolerance (mm): +0.0/-0.25
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @2000 - 10,000nm
Coating: Protected Gold (700-10000nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 85
Edges: Fine Ground
Thickness (mm): 3.00 ±0.25
Type: Flat Mirror
Wavelength Range (µm): 0.7 - 10
Wavelength Range (nm): 700 - 10000
Damage Threshold, Reference: ☐ 0.8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant