

3.1" High Brightness LED Diffuselite, 625nm

See More by [Advanced Illumination](#)



Advanced Illumination Diffuselite LED Illuminators

Stock **#88-499** [CONTACT US](#)

- 1 + **₹91,872.00**

ADD TO CART

Qty 1+
₹91,872.00

Volume Pricing
Request Quote

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color: Red
Height (mm): 7.00
Model Number: DL194-625-IC
Operating Temperature (°C): 0 to 65

Outer Diameter (mm): 133.4
Wavelength (nm): 625.00
Working Distance (mm): 13 - 50
LED Lifetime (hours): 50,000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Light Distribution (%): ±10 Edge to Edge (Dependent on Working Distance)
Number of LEDs: 12.00
Number of Channels: 1.00
Field Coverage (mm): 89.00
Maximum Trigger Frequency (Hz): 30.00
Type of Illumination: LED Illuminator
Note: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Manufacturer: Advanced Illumination
Geometry: Diffuse
Illumination Mode: Constant

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Contains SVHC(s)
