

340nm CWL, 10nm FWHM, 25mm Mounted Diameter



Stock #65-674

CLEARANCE

10 TO 12 DAYS

-

1

+

₹11,740.65

ADD TO CART

Qty 1+
₹11,740.65

Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):

25.00 +0.0/-0.2

Angle of Incidence (°):

0

Optical Density OD (Average):

≥3.0

Clear Aperture CA (mm):

21.0

Center Wavelength CWL (nm):

340.00 ±2

Center Wavelength CWL Tolerance (nm): ±2
Full Width-Half Max FWHM (nm): 10.00 ±2
Full Width-Half Max FWHM Tolerance (nm): ±2
Minimum Transmission (%): ≥25
Operating Temperature (°C): -50 to +75
Coating: Traditional Coated
Surface Quality: 80-50
Thickness Tolerance (mm): ±0.1
Type: Bandpass Filter
Typical Applications: FURAExcitation
Blocking Wavelength Range (nm): 200 - 1200
Construction: Mounted in Black Anodized Ring
Mount Thickness (mm): 7.5 ±0.1

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View