


35" x 47", English Lab Table, Surcharge Applies - Oversized Item

See More by [TMC](#)

Stock #54-257 **2 In Stock**



MRP ₹2,30,534

Price inclusive of all taxes

ADD TO CART



Volume Pricing	
Qty 1+	₹2,30,534 each
Need More?	Request Quote

Product Downloads	
STEP:step	PDF Drawing:pdf
IGES:igs	eDrawing:eprt
EO Spec Sheet	Download All

General

Type: English

Physical & Mechanical Properties

Thickness (mm): 50.00	Length (inches): 47.0
Width (inches): 35.0	Construction: Stainless Steel (400 Series) Top and Bottom Plates, Plated Steel Honeycomb Core, High Pressure Laminate Core Sidewalls
Core Cell Area (cm²): ≤3	Flatness (mm): 0.13
Weight (lbs): 111.0	Top Skin: 430 Series Ferromagnetic Stainless Steel
Core Density: 13.3 lb/ft ³ (230 kg/m ³)	Core Cell Size: < 0.5 in. ² (3 cm ²)
Core Shear Modulus: 275,000 PSI (19300 kg/cm ²)	Top Skin Thickness: 0.075 in. (2 mm)

Threading & Mounting

Mounting Threads: (1485) ¼-20 Tapped on 1" Centerlines, on 1.5" Corners

Regulatory Compliance

RoHS 2015: [Compliant](#)

Certificate of Conformance: [View](#)

Country of Origin: United States

Imported By: Edmund Optics India Private Limited
267, Greystone

Product Details

- Stainless Steel
- Economically Priced
- Lightweight Design

TMC™ CleanTop® Optical Honeycomb Breadboards are ultra-light (9 lbs/ft², 44kg/m²) breadboards that employ countersunk, tapped holes in a thin top-skin of stainless steel. Top and bottom plates have a matte finish to lower reflectance and are ferromagnetic for mounting with magnetic bases. The tapped mounting holes allow for mounting with our English or Metric posts and post holders, as well as most commonly used optical mounts. TMC™ CleanTop® Optical Honeycomb Breadboards feature holes that are on 1" (25mm) centers with 1.5" (37.5mm) corners. Individually sealed holes allow for easy cleaning of spills

Note: Due to size and weight, shipping method and charges will differ from standard catalog charges; please contact our [Sales Department](#) for detailed information. Also note that these items will not be shipped overnight.

Related Products



Universal Right Angle Brackets



Metric/English and English/Metric Adapter Plates



Post Holders



Breadboard Handles

Frequently Purchased Together



#64-007 - 5mm Diameter
Enhanced Aluminum Coated,
 $\lambda/10$ Mirror
₹9,333

Qty



#65-656 - 656nm CWL, 10nm
FWHM, 12.5mm Mounted Diameter
₹10,594

Qty

Resources

Media Type

? FAQ

Do you have any components that would...

? FAQ

Do your iris diaphragms have mounts for...

GLOSSARY

Axial Runout

FAQ

Glossary

Application Note

Trending in Optics

Video



GLOSSARY
Concentricity

GLOSSARY
Inverted Load Capacity

GLOSSARY
Tangent Arm Drive

[View More](#)