

35.0mm FL, IR-Cut Filter at 650nm, f/2, Micro Video Lens



Stock #66-896 10 TO 12 DAYS

-

1

+

₹6,090.00

ADD TO CART

Qty 1-49
₹6,090.00
Qty 50+
₹4,785.00
Volume Pricing
Request Quote

Get Product Downloads

Length (mm):
23.40

Filter Thread:
M12 x 0.50

Maximum Diameter (mm):
25.0

Maximum Image Circle (mm):
11.00

Horizontal Field of View @ Max Sensor Format: 13.6
Resolution, On-Axis: 160 lp/mm @20% Contrast
Resolution, 0.7 Field: 100 lp/mm @20% Contrast
Resolution, Full Field: 80 lp/mm @20% Contrast
Note: IR Cut-Off Filter Included
Type: M12 Imaging Lens
Focal Length FL (mm): 35.00
Maximum Sensor Format: 2/3"
Working Distance (mm): 400 - ∞
Mount: M12 x0.5 (S-Mount)
Aperture (f/#): f/2
Distortion (%): -1.10 @ Full Field
IR Cut Filter: Yes
Lens Wavelength Range: VIS (IR-Cut Filter)

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View