

**TECHSPEC® 35mm 488nm, Laser Line Polarizing Cube Beamsplitter**



TECHSPEC Laser Line Polarizing Cube Beamsplitters

Stock **#48-877** CLEARANCE 10 TO 12 DAYS

- 1 + **₹21,746.00**

ADD TO CART

Qty 1+

₹21,746.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

**Beam Deviation (arcmin):**  
±3

**Bevel:**  
Protective bevel as needed

**Clear Aperture (%):**  
90.00

**Coating Specification:**  
R<sub>abs</sub> <0.25% @ 488nm

**Construction:**  
Cube

|                                                                     |
|---------------------------------------------------------------------|
| <b>Design Wavelength DWL (nm):</b><br>488                           |
| <b>Dimensions (mm):</b><br>35.0 x 35.0 x 35.0 ±0.1                  |
| <b>Extinction Ratio:</b><br>1000:1                                  |
| <b>P-Polarization Transmission (%):</b><br>>95                      |
| <b>S-Polarization Reflection (%):</b><br>>99.5                      |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">N-BK7</a> |
| <b>Surface Flatness (P-V):</b><br>$\lambda/4$                       |
| <b>Surface Quality:</b><br>40-20                                    |
| <b>Type:</b><br>Linear Polarizer                                    |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |