

TECHSPEC®

35mm 850nm, Laser Line Polarizing Cube Beamsplitter



TECHSPEC Laser Line Polarizing Cube Beamsplitters

Stock **#47-570** 10 TO 12 DAYS

⊖ 1 ⊕

₹37,410.00

ADD TO CART

Qty 1-5
₹37,410.00
Qty 6+
₹29,406.00
Volume Pricing
Request Quote

Get Product Downloads

Beam Deviation (arcmin):
±3

Bevel:
Protective bevel as needed

Clear Aperture (%):
90.00

Coating Specification:

R _{abs} <0.25% @ 850nm
Construction: Cube
Design Wavelength DWL (nm): 850
Dimensions (mm): 35.0 x 35.0 x 35.0 ±0.1
Extinction Ratio: 1000:1
P-Polarization Transmission (%) : >95
S-Polarization Reflection (%) : >99.5
Substrate:  N-BK7
Surface Flatness (P-V): λ/4
Surface Quality: 40-20
Type: Linear Polarizer

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View