

TECHSPEC® 35mm, Aluminum & VIS 0° Coated, N-BK7 Right Angle Prism



N-BK7 Right Angle Prisms

Stock **#48-554** 10 TO 12 DAYS

- 1 + **₹13,485.00**

ADD TO CART

Qty 1-5
₹13,485.00
Qty 6+
₹12,137.00
Volume Pricing
Request Quote

Get Product Downloads



Coating:
VIS 0° & Aluminized

Substrate: ☐
[N-BK7](#)

Surface Quality:
60-40

Type: Right Angle Prism
Dimensional Tolerance (mm): ±0.1
Angle Tolerance (arcmin): ±2
Bevel: Protective bevel as needed
Length of Hypotenuse (mm): 49.50
Length of Legs (mm): 35.00
Image Orientation: Left-Handed
Coating Specification: Hypotenuse: R _{avg} >85% @ 400 - 700nm Legs: R _{avg} ≤0.4% @ 425 - 675nm
Ray Deviation (°): 90
Wavelength Range (nm): 425 - 675
Surface Flatness (P-V): λ/4
Damage Threshold, By Design: ☐ Hypotenuse: 0.3 J/cm ² @ 532nm & 1064nm, 10ns Legs: 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View