

TECHSPEC® 3.5mm, f/5.6 Ci Series Fixed Focal Length Lens



3.5mm Focal Length

Stock #87-548 **1 In Stock**

1 MRP ₹25,185

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-24	₹25,185 each
Qty 25+	₹22,796 each
Need More?	Request Quote

Product Downloads	
STEP:step	PDF Drawing:pdf
IGES:igs	Zemax
eDrawing:eprt	
EO Spec Sheet	

General

Product Family: Ci Series	Type: Fixed Focal Length Lens
----------------------------------	--------------------------------------

Physical & Mechanical Properties

Iris Option: Fixed	Length (mm): 39.38
Maximum Diameter (mm): 50	Outer Diameter (mm): 50
Weight (g): 97	Maximum Rear Protrusion (mm): 2.64
Diameter (mm): 26.50	

Optical Properties

Horizontal Field of View @ Max Sensor Format: 41.2mm - 102.8°	Field of View at Max Sensor Format: Horizontal: 41.2mm - 102.3° Vertical: 26.8mm - 82.3° Diagonal: 63.5mm - 117°
Horizontal Field of View, 1/1.8" Sensor: 41.2mm - 102.8°	Horizontal Field of View, 1/2" Sensor: 29.5mm - 87.2°
Horizontal Field of View, 1/3" Sensor: 23.0mm - 74.4°	Horizontal Field of View, 1/4" Sensor: 16.3mm - 57.4°
Maximum Image Circle (mm): 9.00	Numerical Aperture NA, Object Side: 0.0205
Number of Elements (Groups): 8 (7)	Focal Length FL (mm): 3.50

Working Distance (mm):	0 - ∞	Aperture (f/#):	f/5.6
Coating:	425 - 675nm BBAR	Coating Specification:	425 - 675nm BBAR
Entrance Pupil Position (mm):	15.27	Object Space Principal Plane (mm):	18.31
Image Space Principal Plane (mm):	7.49	Maximum Distortion (%):	-20.94
Exit Pupil Position (mm):	-15.28	Lens Wavelength Range:	VIS

Sensor

Maximum Sensor Format:	1/1.8"	Pixel Size (µm):	2.74
-------------------------------	--------	-------------------------	------

Threading & Mounting

Filter Thread:	M105 x 1.00 (Male)	Filter Thread Adapter:	#89-848 (Required)
Front Thread:	M50.0 x 0.5 (Male)	Mount:	C-Mount

Environmental & Durability Factors

Storage Temperature (°C):	-20 to +60	Type of Ruggedization:	Industrial (Fixed Aperture with Simplified Mechanics)
----------------------------------	-------------------	-------------------------------	---

Regulatory Compliance

Certificate of Conformance:	View		
Country of Origin:	China	Imported By:	Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91-80-6845 0000

Product Details

- Up to 2/3", C-Mount Lens
- Up to 7.5 MegaPixels, 2.8µm Pixel Size Sensors
- Instrumentation (Ci) Versions of our C Series Lenses with Streamlined Mechanical Designs and Fixed Apertures
- 3.5mm to 50mm Focal Length
- **Ruggedized (Cr) Designs** Also Available

TECHSPEC® Ci Series Fixed Focal Length Lenses are a streamlined version of our C Series Fixed Focal Length Lenses. They feature the same low lens-to-lens variation and broadband anti-reflection (BBAR) coating for maximum light transmission, while offering reduced weight and size. An adjustable, lockable focus allows for setting and locking the best focus position for instrumentation integration. TECHSPEC® Ci Series Fixed Focal Length Lenses are designed specifically for volume integration into applications such as factory inspection and automation to benchtop biomedical devices. The Ci Series offers a wide range of aperture options, ensuring maximum flexibility of resolution, throughput, and depth of field.

Edmund Optics has created a family of high performance optical designs (the C Series family) and developed 6 customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the C Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:

- **C Series:** Features locking cam focus and iris adjustment and is the most adjustable version of these optical designs; they are the typical high quality machine vision lenses. Also available with a **VIS-NIR Broadband Anti-Reflection (BBAR) Coating**.
- **Ci Series:** Simplified mechanics featuring fixed apertures with compact housing. **Industrial Ruggedization** for reduced size, cost, and locked focus.
- **Cr Series:** All optics glued in place and a locking C-clamp focus ring. **Stabilized Ruggedization** for reduced pixel shift and improved focus stability.
- **Cx Series:** Modular, flexible mechanics allows lenses to be taken apart for easy integration of accessories such as liquid lenses, apertures, and more.

- **Liquid Lens Cx Series:** Designed with an integrated liquid lens for quick autofocus.
- **Cw Series:** Waterproof, designed to meet IEC **Ingress Protection** Code IPX7 and IPX9K.

Technical Information

#87-548, 3.5mm, f/5.6 Ci Series Fixed Focal Length Lens, Distortion Plot

#87-548, 3.5mm, f/5.6 Ci Series Fixed Focal Length Lens, Relative Illumination Plot

#87-548, 3.5mm, f/5.6 Ci Series Fixed Focal Length Lens, Working Distance versus Field of View Plot

#87-548, 3.5mm, f/5.6 Ci Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 75mm Working Distance, f5.6

#87-548, 3.5mm, f/5.6 Ci Series Fixed Focal Length Lens, Depth of Field Plot, 75mm Working Distance, f5.6

#87-548, 3.5mm, f/5.6 Ci Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 150mm Working Distance, f5.6

#87-548, 3.5mm, f/5.6 Ci Series Fixed Focal Length Lens, Depth of Field Plot, 150mm Working Distance, f5.6

Focal Length	A	B	C	D
6mm	M34.0 x 0.5	47.8mm	34mm	1.17mm
12mm	M22.0 x 0.75	29.0mm	22mm	0.96mm
16mm	M22.0 x 0.75	40.8mm	22mm	1.09mm
25mm	M22.0 x 0.75	29.9mm	22mm	1.33mm
35mm	M25.5 x 0.5	41mm	22.5mm	3.82mm
50mm	M30.5 x 0.5	49.5mm	30.5mm	2.06mm

Accessories

Note: Compatible accessories for individual stock numbers may vary. If unsure about which accessories work with your products, please contact us [here](#).

	Title	Compare	Stock Number	Price	Buy
MORE+	Filter Adapter M105 x 1.0 from M50 x 0.5 (Female)		#89-848	₹6,425 Request Quote	7 In Stock <input type="text" value="1"/>

Frequently Purchased Together



#62-274 - 2/3" Format C-Mount Fisheye Lens 1.8mm FL
₹1,00,890

Qty



#86-592 - 6mm, f/1.8 Ci Series Fixed Focal Length Lens
₹20,481

Qty



#14-156 - M6 and 1/4-20 Mounting Plate for Alvim
₹1,912











































Qty





























































#87-554 - 4.5mm, f/5.6 Ci Series Fixed Focal Length Lens
₹25,185

















































Qty




















































Compatible Cameras














































	Title	Type	Compare	Stock Number	Price	Buy
 	LUCID Vision Labs Phoenix™ PHX023S-CC, Sony IMX392, 2.3MP, Color Camera	Color Camera		#13-662	₹39,400 Request Quote	CONTACT US <input type="text" value="1"/> 
 	LUCID Vision Labs Phoenix™ PHX023S-CC-IX, Sony IMX392, 2.3MP, Color Camera	Color Camera		#13-668	₹39,400 Request Quote	CONTACT US <input type="text" value="1"/> 
 	LUCID Vision Labs Phoenix™ PHX023S-MC, Sony IMX392, 2.3MP, Monochrome Camera	Monochrome Camera		#13-661	₹39,400 Request Quote	CONTACT US <input type="text" value="1"/> 
 	LUCID Vision Labs Phoenix™ PHX023S-MC-IX, Sony IMX392, 2.3MP, Monochrome Camera	Monochrome Camera		#13-667	₹39,400 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-240m, 1/2.3" 2.35MP C-Mount, USB 3.0 Monochrome Camera	Monochrome Camera		#17-085	₹40,356 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-240c, 1/2.3" 2.35MP C-Mount, USB 3.0 Color Camera	Color Camera		#17-086	₹41,418 Request Quote	2 In Stock <input type="text" value="1"/> 
 	Basler ace2 a2A1920-160umBAS Monochrome USB3 Basic Camera	Monochrome Camera		#16-617	₹42,692 Request Quote	2 In Stock <input type="text" value="1"/> 
 	Basler ace2 a2A1920-51gmBAS Monochrome GigE Basic Camera	Monochrome Camera		#16-593	₹42,692 Request Quote	2 In Stock <input type="text" value="1"/> 
 	BFS-PGE-13Y3C-C PoE GigE Blackfly® S, Color Camera	Color Camera		#36-559	₹44,073 Request Quote	CONTACT US <input type="text" value="1"/> 
 	BFS-PGE-13Y3M-C PoE GigE Blackfly® S, Monochrome Camera	Monochrome Camera		#36-558	₹44,073 Request Quote	1 In Stock <input type="text" value="1"/> 
 	BFS-U3-23S3C-C USB 3.1 Blackfly® S, Color Camera	Color Camera		#12-748	₹44,710 Request Quote	2 In Stock <input type="text" value="1"/> 
 	BFS-PGE-23S3C-C PoE GigE Blackfly® S, Color Camera	Color Camera		#12-754	₹44,710 Request Quote	CONTACT US <input type="text" value="1"/> 
 	BFS-U3-23S3M-C USB 3.1 Blackfly® S, Monochrome Camera	Monochrome Camera		#12-747	₹44,710 Request Quote	1 In Stock <input type="text" value="1"/> 
 	BFS-PGE-23S3M-C PoE GigE Blackfly® S, Monochrome Camera	Monochrome Camera		#12-753	₹44,710 Request Quote	CONTACT US <input type="text" value="1"/> 





	Title	Type	Compare	Stock Number	Price	Buy
MORE+ 	LUCID Vision Labs Triton™ TRI023S-CC, Sony IMX392, 2.3MP, Color Camera	Color Camera		#13-714	₹44,816 Request Quote	3 In Stock <input type="text" value="1"/> 
MORE+ 	LUCID Vision Labs Triton™ TRI023S-MC, Sony IMX392, 2.3MP, Monochrome Camera	Monochrome Camera		#13-713	₹44,816 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	Basler ace2 a2A1920-51gcBAS Color GigE Basic Camera	Color Camera		#16-594	₹45,029 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	Allied Vision Alvium G1-240m, 1/2.3" 2.4MP C-Mount, GigE PoE Monochrome Camera	Monochrome Camera		#23-543	₹45,666 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	Basler ace2 a2A1920-160ucBAS Color USB3 Basic Camera	Color Camera		#16-618	₹46,197 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	Allied Vision Alvium G1-240c, 1/2.3" 2.4MP C-Mount, GigE PoE Color Camera	Color Camera		#23-544	₹46,728 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	Allied Vision Alvium 1800 U-319m, 1/1.8" 3.2MP C-Mount, USB 3.0 Monochrome Camera (Partial Housing)	Monochrome Camera		#14-875	₹49,149 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	LUCID Vision Labs Phoenix™ PHX032S-CC, Sony IMX265, 3.2 MP, Color Camera	Color Camera		#11-465	₹49,808 Request Quote	3 In Stock <input type="text" value="1"/> 
MORE+ 	LUCID Vision Labs Phoenix™ PHX032S-CC-IX, Sony IMX265, 3.2 MP, Color Camera	Color Camera		#13-678	₹49,808 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	LUCID Vision Labs Phoenix™ PHX032S-MC, Sony IMX265, 3.2 MP, Monochrome Camera	Monochrome Camera		#11-464	₹49,808 Request Quote	2 In Stock <input type="text" value="1"/> 
MORE+ 	LUCID Vision Labs Phoenix™ PHX032S-MC-IX, Sony IMX265, 3.2 MP, Monochrome Camera	Monochrome Camera		#13-677	₹49,808 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	Allied Vision Alvium 1800 U-319c, 1/1.8" 3.2MP C-Mount, USB 3.0 Color Camera (Partial Housing)	Color Camera		#14-876	₹50,095 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	BFS-U3-13Y3C-C USB 3.1 Blackfly® S, Color Camera	Color Camera		#36-452	₹50,976 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	BFS-U3-13Y3M-C USB 3.1 Blackfly® S, Monochrome Camera	Monochrome Camera		#36-451	₹50,976 Request Quote	2 In Stock <input type="text" value="1"/> 

	Title	Type	Compare	Stock Number	Price	Buy
MORE+ 	BFS-PGE-14Y3M-C. PoE GigE Blackfly® S, Monochrome Camera	Monochrome Camera		#22-074	₹50,976 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	Basler ace acA1300-200um Monochrome USB 3.0 Camera	Monochrome Camera		#33-978	₹54,162 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	Basler ace acA1300-75gm Monochrome GigE Camera	Monochrome Camera		#33-986	₹54,162 Request Quote	2 In Stock <input type="text" value="1"/> 
MORE+ 	LUCID Vision Labs Triton™ TRI032S-CC, Sony IMX265, 3.2MP, Color Camera	Color Camera		#13-716	₹55,224 Request Quote	4 In Stock <input type="text" value="1"/> 
MORE+ 	LUCID Vision Labs Triton™ TRI032S-MC, Sony IMX265, 3.2MP, Monochrome Camera	Monochrome Camera		#13-715	₹55,224 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	Allied Vision Alvium 1800 U-319m, 1/1.8" 3.2MP C-Mount, USB 3.0 Monochrome Camera	Monochrome Camera		#14-871	₹56,286 Request Quote	17 In Stock <input type="text" value="1"/> 
MORE+ 	Allied Vision Alvium 1800 U-319m, 1/1.8" 3.2MP C-Mount, Right Angle USB 3.1 Monochrome Camera	Monochrome Camera		#14-873	₹56,286 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	Basler ace2 a2A1920-160umPRO Monochrome USB3 Pro Camera	Monochrome Camera		#16-629	₹56,817 Request Quote	2 In Stock <input type="text" value="1"/> 
MORE+ 	Basler ace2 a2A1920-51gmPRO Monochrome GigE Pro Camera	Monochrome Camera		#16-605	₹56,817 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	Allied Vision Alvium 1800 U-319c, 1/1.8" 3.2MP C-Mount, USB 3.0 Color Camera	Color Camera		#14-872	₹57,348 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	Allied Vision Alvium 1800 U-319c, 1/1.8" 3.2MP C-Mount, Right Angle USB 3.1 Color Camera	Color Camera		#14-874	₹57,348 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	M1280, 1/2" Monochrome, DALSA Genie Nano GigE PoE Camera	Monochrome Camera		#34-952	₹57,879 Request Quote	3 In Stock <input type="text" value="1"/> 
MORE+ 	Basler ace acA1300-200uc Color USB 3.0 Camera	Color Camera		#33-979	₹58,410 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	Basler ace acA1300-75gcE Color GigE Camera	Color Camera		#33-987	₹58,410 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	Basler ace2 a2A1920-51gcPRO Color GigE Pro Camera	Color Camera		#16-606	₹59,472 Request Quote	CONTACT US <input type="text" value="1"/> 

	Title	Type	Compare	Stock Number	Price	Buy
 	BFS-PGE-31S4C-C PoE GigE Blackfly® S, Color Camera	Color Camera		#11-528	₹60,003 Request Quote	CONTACT US <input type="text" value="1"/> 
 	BFS-U3-31S4C-C USB 3.1 Blackfly® S, Color Camera	Color Camera		#12-750	₹60,003 Request Quote	CONTACT US <input type="text" value="1"/> 
 	BFS-PGE-31S4M-C PoE GigE Blackfly® S, Monochrome Camera	Monochrome Camera		#11-527	₹60,003 Request Quote	2 In Stock <input type="text" value="1"/> 
 	BFS-U3-31S4M-C USB 3.1 Blackfly® S, Monochrome Camera	Monochrome Camera		#12-749	₹60,003 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Basler ace2 a2A1920-160ucPRO Color USB3 Pro Camera	Color Camera		#16-630	₹60,534 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Basler ace acA2040-35gm Monochrome GigE Camera	Monochrome Camera		#35-915	₹60,534 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Alvium G1-319m, 1/1.8" 3.2MP C-Mount, GigE PoE Monochrome Camera	Monochrome Camera		#23-547	₹61,596 Request Quote	CONTACT US <input type="text" value="1"/> 
 	BFLY-PGE-31S4M/C-C 1/1.8" Blackfly® PoE GigE Color Camera	Color Camera		#34-510	₹62,127 Request Quote	CONTACT US <input type="text" value="1"/> 
 	C1280-IR, 1/2" Color, DALSA Genie Nano GigE PoE Camera	Color Camera		#34-953	₹62,127 Request Quote	1 In Stock <input type="text" value="1"/> 
 	BFLY-PGE-31S4M/C-C 1/1.8" Blackfly® PoE GigE Monochrome Camera	Monochrome Camera		#34-511	₹62,127 Request Quote	2 In Stock <input type="text" value="1"/> 
 	Allied Vision Alvium G1-319c, 1/1.8" 3.2MP C-Mount, GigE PoE Color Camera	Color Camera		#23-548	₹62,658 Request Quote	3 In Stock <input type="text" value="1"/> 
 	M1280, 1/2" NIR, Teledyne DALSA Genie Nano GigE PoE Camera	NIR Camera		#14-675	₹62,658 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Basler ace acA2040-35gc Color GigE Camera	Color Camera		#35-916	₹63,720 Request Quote	2 In Stock <input type="text" value="1"/> 
 	M2020, 1/1.8" Monochrome, DALSA Genie Nano GigE PoE Camera	Monochrome Camera		#34-960	₹64,251 Request Quote	2 In Stock <input type="text" value="1"/> 
 	C2020-IR, 1/1.8" Color, DALSA Genie Nano GigE PoE Camera	Color Camera		#34-961	₹65,844 Request Quote	2 In Stock <input type="text" value="1"/> 
 	IDS U3-3140CP-C-HQ, USB 3.0, 1/2" Color Camera	Color Camera		#24-079	₹69,030 Request Quote	3 In Stock <input type="text" value="1"/> 

	Title	Type	Compare	Stock Number	Price	Buy
 	IDS U3-3140CP-M-GL, USB 3.0, 1/2" Monochrome Camera	Monochrome Camera		#24-080	₹69,030 Request Quote	2 In Stock <input type="text" value="1"/> 
 	IDS U3-3270CP-C-HQ REV.2.2, USB 3.0, 1/1.8" Color Camera	Color Camera		#16-528	₹71,154 Request Quote	2 In Stock <input type="text" value="1"/> 
 	Allied Vision Mako G-192B 1/1.8" Monochrome CMOS Camera	Monochrome Camera		#33-516	₹71,154 Request Quote	3 In Stock <input type="text" value="1"/> 
 	Allied Vision Mako G-192C 1/1.8" Color CMOS Camera	Color Camera		#33-517	₹73,278 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Basler ace acA2040-55um Monochrome USB 3.0 Camera	Monochrome Camera		#35-921	₹74,340 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Basler ace acA2040-55uc Color USB 3.0 Camera	Color Camera		#35-922	₹76,464 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Basler ace acA1600-60gm Monochrome GigE Camera	Monochrome Camera		#88-330	₹82,836 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Basler ace acA1600-60gc Color GigE Camera	Color Camera		#88-331	₹87,084 Request Quote	2 In Stock <input type="text" value="1"/> 
 	Allied Vision Mako G-319 1/1.8" Monochrome CMOS Camera	Monochrome Camera		#36-174	₹89,208 Request Quote	2 In Stock <input type="text" value="1"/> 
 	Allied Vision Mako G-319 1/1.8" Color CMOS Camera	Color Camera		#36-175	₹91,332 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Allied Vision Manta G-0319 1/1.8" Color Camera	Color Camera		#34-717 CLEARANCE	₹92,283 Request Quote	2 In Stock <input type="text" value="1"/> 
 	BFS-U3-32S4C-C USB 3.1 Blackfly® S, Color Camera	Color Camera		#36-454	₹96,111 Request Quote	1 In Stock <input type="text" value="1"/> 
 	BFS-U3-32S4M-C USB 3.1 Blackfly® S, Monochrome Camera	Monochrome Camera		#36-453	₹96,111 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Basler ace acA2040-120um Monochrome USB 3.0 Camera	Monochrome Camera		#35-923	₹1,04,076 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Basler ace acA2040-120uc Color USB 3.0 Camera	Color Camera		#35-924	₹1,06,200 Request Quote	2 In Stock <input type="text" value="1"/> 
 	Allied Vision Manta G-0319 1/1.8" Monochrome Camera	Monochrome Camera		#34-716	₹1,07,262 Request Quote	1 In Stock <input type="text" value="1"/> 
 	IDS U3-3070CP-C-HQ, USB 3.0, 1/1.8" Color Camera	Color Camera		#16-512	₹1,08,324 Request Quote	2 In Stock <input type="text" value="1"/> 

	Title	Type	Compare	Stock Number	Price	Buy
 	IDS U3-3070CP-M-GL, USB 3.0, 1/1.8" Monochrome Camera	Monochrome Camera		#16-513	₹1,08,324 Request Quote	2 In Stock <input type="text" value="1"/> 
 	Allied Vision Manta G-319C Color CMOS PoE Camera	Color Camera		#37-511	₹1,13,634 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Manta G-319B Monochrome CMOS PoE Camera	Monochrome Camera		#37-510	₹1,13,634 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Pixelink M-Series M1C-CYL Microscopy Color Camera	Color Microscopy Camera		#17-813	₹1,14,696 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Pixelink M-Series M1M-CYL Microscopy Monochrome Camera	Monochrome Microscopy Camera		#17-814	₹1,14,696 Request Quote	CONTACT US <input type="text" value="1"/> 
 	GS3-U3-32S4C-C 1/1.8" FLIR Grasshopper®3 High Performance USB 3.0 Color Camera	Color Camera		#33-535	₹1,22,661 Request Quote	1 In Stock <input type="text" value="1"/> 
 	GS3-U3-32S4M-C 1/1.8" FLIR Grasshopper®3 High Performance USB 3.0 Monochrome Camera	Monochrome Camera		#33-534	₹1,22,661 Request Quote	2 In Stock <input type="text" value="1"/> 
 	Pixelink PL-D721MU-BL, 1/2" 1.3MP, Board Level USB 3.0 Monochrome Camera	Monochrome Camera		#89-380	₹1,48,680 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Pixelink PL-D721MU-T, 1/2" 1.3MP, C-Mount USB 3.0 Monochrome Camera	Monochrome Camera		#89-378	₹1,60,362 Request Quote	1 In Stock <input type="text" value="1"/> 
 	M2050, 1/1.8" Monochrome, Teledyne DALSA Genie Nano 5GigE PoE Camera	Monochrome Camera		#16-024	₹1,69,920 Request Quote	4 In Stock <input type="text" value="1"/> 
 	C2050-IR, 1/1.8" Color, Teledyne DALSA Genie Nano 5GigE PoE Camera	Color Camera		#16-025	₹1,71,513 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Oryx® ORX-10GS-32S4C-C Color 10GigE	Color Camera		#19-797	₹1,88,505 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Oryx® ORX-10GS-32S4M-C Mono 10GigE	Monochrome Camera		#19-796	₹1,88,505 Request Quote	1 In Stock <input type="text" value="1"/> 
 	PL-D721-AF-ED Pixelink USB 3.0 Autofocus Color Camera	Color Camera		#34-776	₹2,17,710 Request Quote	1 In Stock <input type="text" value="1"/> 
 	PL-D721-AF-ED Pixelink USB 3.0 Autofocus Monochrome Camera	Monochrome Camera		#34-775	₹2,17,710 Request Quote	1 In Stock <input type="text" value="1"/> 

	Title	Type	Compare	Stock Number	Price	Buy
MORE+ 	Lumenera INFINITY5 5-3 Microscopy Color Camera	Color Microscopy Camera		#16-678	₹3,95,595 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	Lumenera INFINITY5 5-3 Microscopy Monochrome Camera	Monochrome Microscopy Camera		#16-677	₹3,95,595 Request Quote	1 In Stock <input type="text" value="1"/> 

Resources

Media Type

- Application Note
- Video
- Trending in Optics
- Published Article
- FAQ
- Glossary
- Technical Tool

APPLICATION NOTE

Anti-Reflection (AR) Coatings

APPLICATION NOTE

An Introduction to Optical Coatings

VIDEO

Wavelength and f#

APPLICATION NOTE

Understanding Focal Length and Field of View

APPLICATION NOTE

Introduction to Modulation Transfer Function

VIDEO

LIGHT TALK - EPISODE 5: Ruggedized Imaging

[View More](#)