

3600 Grooves/mm, 25mm Square, UV Holographic Grating



Reflective Holographic Gratings

Stock **#43-228** 10 TO 12 DAYS

⊖ 1 ⊕ **₹14,442.00**

ADD TO CART

Qty 1+
₹14,442.00
Volume Pricing
Request Quote

Get Product Downloads



Groove Density (grooves/mm):
3600

Wavelength Range (nm):
250 - 400

Dimensions (mm):
25.0 x 25.0 ±0.5

Coating:
Bare Aluminum

Construction: Holographic Grating
Length (mm): 25.00
Substrate:  Float Glass
Thickness (mm): 9.50 ±0.5
Type: Reflective Diffraction Grating
Wavelength: UV
Width (mm): 25.00
Alignment of Grooves to Edge (°): ±0.5
Absolute Peak Efficiency, Typical (%): 56
Peak Efficiency Avg, Typical (%): >39

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View
