

3.74mm FL, High Resolution, f/1.6, Micro Video Lens



Stock #11-323 10 TO 12 DAYS

-

1

+

₹6,438.00

ADD TO CART

Qty 1-49
₹6,438.00
Qty 50+
₹4,959.00
Volume Pricing
Request Quote

Get Product Downloads

Length (mm):
24.04

Maximum Diameter (mm):
19.0

Maximum Image Circle (mm):
8.00

Horizontal Field of View @ Max Sensor Format:
99

Resolution, On-Axis: 100 lp/mm @61.7% Contrast
Resolution, 0.7 Field: 100 lp/mm @56.8% Contrast
Resolution, Full Field: 100 lp/mm @48.2% Contrast
Note: High Resolution
TV Distortion (%): -22.4
Type: M12 Imaging Lens
Focal Length FL (mm): 3.74
Maximum Sensor Format: 1/2"
Working Distance (mm): 400 - ∞
Mount: M12 x0.5 (S-Mount)
Aperture (f/#): f/1.6
IR Cut Filter: Yes
Lens Wavelength Range: VIS (IR-Cut Filter)

Regulatory Compliance

Reach 205: Compliant
Certificate of Conformance: View