

TECHSPEC® 38.1mm Dia. 1064nm, Nd:YAG Laser Line Beam Sampler



TECHSPEC® Nd:YAG Laser Line Beam Samplers

Stock **#39-020** 10 TO 12 DAYS

- 1 + **₹16,530.00**

ADD TO CART

Qty 1-5
₹16,530.00
Qty 6+
₹14,877.00
Volume Pricing
Request Quote

Get Product Downloads

Angle of Incidence (°):
0 ±5

Clear Aperture (%):
90

Coating:
Laser V-Coat (1064nm)

Coating Specification:

R _{abs} <0.25% @ 1064nm
Design Wavelength DWL (nm): 1064
Diameter (mm): 38.10 +0.00/-0.10
Index of Refraction n_d: 1.458
Parallelism (arcmin): <3
Substrate: ☐ Fused Silica (Coming 7980)
Surface Flatness (P-V): λ/10
Surface Quality: 10-5
Thickness (mm): 6.35 ±0.20
Type: Beam Sampler
Damage Threshold, By Design: ☐ 15 J/cm² @ 1064nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View