

38.1mm Dia., Aluminum Coated, Aluminum Substrate Mirror



Metal Substrate Mirrors

Stock **#47-115** 10 TO 12 DAYS

- 1 +

₹18,270.00

ADD TO CART

Qty 1-5
₹18,270.00
Qty 6+
₹16,443.00
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
38.10 +0.00/-0.38

Substrate: Aluminum 6061-T6

Surface Quality:
80-50

Coating Specification:

R_{avg} >85% @ 400 - 700nm
R_{avg} >70% @ 700 - 2000nm
R_{avg} >97% @ 2 - 12μm

Coating:
Protected Aluminum (400-12000nm)

Coating Type:
Metal

Clear Aperture (%):
90

Mounting Threads:
6-32 TPI Tapped Holes

Surface Roughness (Angstroms):
<175

Thickness (mm):
9.50

Type:
Flat Mirror

Wavelength Range (μm):
0.4 - 12

Wavelength Range (nm):
400 - 12000

Surface Flatness (RMS):
λ/4

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 235:
[Compliant](#)