

## 38.1mm Diameter, 4-6λ Mirror



4-6λ First Surface Mirrors

Stock **#69-247** **7 In Stock**

1  MRP ₹3,103

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹3,103 each
Qty 6-25	₹2,421 each
Qty 26-99	₹2,018 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Flat Mirror **Type:**

#### Physical & Mechanical Properties

38.10 ±0.76 **Diameter (mm):**

**Thickness (mm):**

3.00 Nominal

Protective as needed **Bevel:**

>90 **Clear Aperture (%):**

## Optical Properties

Metal **Coating Type:**

Protected Aluminum (400-700nm) **Coating:**

4 - 6λ **Surface Flatness (P-V):**

400 - 700 **Wavelength Range (nm):**

Float Glass **Substrate:** □

45.00 **Angle of Incidence (°):**

R<sub>avg</sub> >85% @400 - 700nm **Coating Specification:**

80-50 **Surface Quality:**

## Regulatory Compliance

**Compliant** **RoHS 2015:**

**View** **Certificate of Conformance:**

**Compliant** **Reach 247:**

United States **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000


## Product Details

- Wide Variety of Shapes and Sizes Available
- >85% Reflection of Visible Light
- [Contact Us](#) for Custom Sizes

4 - 6λ First Surface Mirrors are an economical choice for a wide range of applications. First surface mirrors feature high reflectivity coating deposited on the front surface of the glass substrate. The mirrors are available in circular, square, and rectangular dimensions. Rectangular 4 - 6λ First Surface Mirrors are ideal for applications requiring the mirror to be mounted at 45° in order to produce a 90° bend in the light path. The mirrors have a protected aluminum coating, and they reflect greater than 85% of visible light.

Can't find what you need? Get a quick [custom quote](#).

## Technical Information



**Quote Your Size**

**Compatible Mounts**