

TECHSPEC® 38.1mm Mounted Corner Cube Retroreflector



Mounted N-BK7 Corner Cube Retroreflectors



Stock **#45-190** 10 TO 12 DAYS

- 1 +

₹39,585.00

ADD TO CART

Qty 1-5
₹39,585.00
Qty 6+
₹31,668.00
Volume Pricing
Request Quote

Get Product Downloads



Beam Deviation (arcsec):
±3

Coating:
Silver with protective overcoat

Diameter Tolerance (mm): +0.0/-0.1
Substrate: N-BK7
Inner Diameter (mm): 38.10
Outer Diameter (mm): 50.80
Surface Quality: 60-40
Mounting Threads: (2) 1/4-20 Tapped Holes
Type: Retroreflector
Housing Tolerance (mm): Outer Diameter: +0/-0.5, Height: ±0.25
Image Orientation: Left-Handed
Coating Specification: Reflective Surfaces: R_{abs} > 97% FROM400 - 2500nm @ 0° AOI R_{avg} > 98% FROM400 - 2500nm @ 0° AOI
Ray Deviation (°): 180
Wavelength Range (nm): 500 - 10000
Surface Flatness (P-V): λ/8

Regulatory Compliance

RoHS 2015: Not Compliant
Certificate of Conformance: View