

TECHSPEC[®] 18.0mm Dia. x 50.0mm FL, VIS 0°, Inked, Plano-Convex Lens



Stock #38-316-INK 17 TO 22 D=DAYS

[Other Coating Options](#)

-

1

+

₹4,437.00

ADD TO CART

Qty 1-9
₹4,437.00
Qty 10+
₹4,002.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
18.00 ±0.025

Effective Focal Length EFL (mm):
50.00 @ 587.6nm

Back Focal Length BFL (mm): 48.09
Coating: VIS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 2.90 ±0.10
Edge Thickness ET (mm): 1.28
Radius R₁ (mm): 25.84
Clear Aperture CA (mm): 17
f/#: 2.78
Numerical Aperture NA: 0.18
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 425 - 675
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View