

[See all 4 Products in Family](#)

## 3mm Dia. x 12mm FL, Commercial Grade, Plano-Convex Lens



Stock #23-060 CLEARANCE 1 In Stock

[Other Coating Options](#)

1  MRP ₹2,069

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹2,069 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Plano-Convex Lens **Type:**

### Physical & Mechanical Properties

3.00 +0.00/-0.10 **Diameter (mm):**

6.00 **Centering (arcmin):**

**Center Thickness CT (mm):**

1.50

Edge Thickness ET (mm):

1.32

Clear Aperture CA (mm):

≥2.55

### Optical Properties

Effective Focal Length EFL (mm):

12.00

Back Focal Length BFL (mm):

11.01

Coating:

Uncoated

Substrate:

N-BK7

Focal Length Tolerance (%):

±1

Radius  $R_1$  (mm):

6.20

f#:

4.00

Numerical Aperture NA:

0.13

### Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

China

Imported By:

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91-80-6845 0000

## Product Details

- Feature Standard Designs and Specifications
- Also Available with [MgF<sub>2</sub> Coating](#)
- For More Options, View [Precision Quality Plano-Convex \(PCX\) Lenses](#)

Plano convex lenses (PCX) have one flat and one outward curving face and a positive focal length. They are ideal for collecting and focusing light in imaging applications. They are also useful in a variety of applications involving emitters, detectors, lasers, and fiber optics. Commercial Grade Uncoated Plano-Convex(PCX) Lenses offer commercial quality, at an affordable price.

## Technical Information

