

TECHSPEC®

3" Dia, 30" FL UV Enhanced Alum., Spherical Mirror



Stock #43-559

10 TO 12 DAYS

-

1

+

₹23,490.00

ADD TO CART

Qty 1-9
₹23,490.00
Qty 10+
₹19,967.00
Volume Pricing
Request Quote

Get Product Downloads



Substrate:

BOROFLOAT®

Focal Length Tolerance (%):
±2

Surface Quality:
60-40

Surface Accuracy:

N4
Diameter (inches): 3.0
Diameter (mm): 76.20 +1.0/-0
Diameter Tolerance (inches): +0.04/-0
Effective Focal Length EFL (inches): 30.00
Effective Focal Length EFL (mm): 762.00
Radius of Curvature (mm): 1,524.00
Aperture (f/#): f/10
Coating: Enhanced Aluminum (250-700nm)
Coating Specification: R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm
Coating Type: Metal
Back Surface: Ground
Edge Thickness ET (inches): 0.50
Edge Thickness ET (mm): 12.70
Edge Thickness Tolerance (%): +0.0/-15
Type: Spherical Mirror
Wavelength Range (nm): 250 - 700
Damage Threshold, Reference: 0.5 J/cm ² @ 355nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant