

[See all 19 Products in Family](#)

4" x 4" 470nm Edge-Lit Backlight

See More by [Advanced Illumination](#)



Stock #73-902 **NEW** 1 In Stock

1 MRP ₹86,553

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹86,553 each
Need More?	Request Quote

Product Downloads

General

Model Number:
BX2-100100470IC

LED Lifetime (hours):
50,000

Type of Illumination:
LED Illuminator

Manufacturer:
Advanced Illumination

Geometry:

Backlight

Illumination Mode:

Constant

Physical & Mechanical Properties

Dimensions (mm):

157.5 L x 157.5 W x 19.1 T

Active Area (inches):

4 x 4

Optical Properties

Color:

Blue

Wavelength (nm):

470

Hardware & Interface Connectivity

Power Supply:

Power Supply Required and Sold Separately.

USA: [#66-855](#)

Europe: [#66-855](#)

Japan: [#89-513](#)

Korea: [#33-773](#)

China: [#66-855](#)

Environmental & Durability Factors

Operating Temperature (°C):

0 - 35

Regulatory Compliance

RoHS 2015:

[Exempt](#)

Certificate of Conformance:

[View](#)

Reach 247:

[Contains SVHC\(s\)](#)

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91-80-6845 0000

Product Details

- 30% Brighter than Comparable Surface Mount Light
- Uniform, Low Heat Illumination

Advanced Illumination Side-Fired LED Backlights are high performance alternatives to surface mount lights. Advanced Illumination Side-Fired LED Backlights provide uniform, low heat illumination that is 30% brighter than surface mount lights of equal size. To simplify system integration, these backlights include mounting brackets and mounting channels for M6 nuts.

Note: Required 24V power supply [#66-855](#). [Accessories for Advanced Illumination products](#) are available and sold separately. Units cannot be intensity controlled.