

40 lp/mm, 1" x 3", Fused Silica, Ronchi Ruling



Stock #57-886 CLEARANCE **1 In Stock**

MRP ₹39,931

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1-4	₹39,931 each
Qty 5+	₹38,020 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties

Length (inches):
3.00

Pattern Size (mm):
12.7 x 25.4

Thickness (mm):
1.10

Width (inches):
1.00

Optical Properties

Vacuum Deposited Chrome
Coating:
40.00
Frequency (lp/mm):

Fused Silica (Corning 7980)
Substrate: □
3.00
Optical Density OD (Average):

Regulatory Compliance

Compliant
RoHS 2015:

View
Certificate of Conformance:

Compliant
Reach 240:

United States
Country of Origin:

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91-80-6845 0000

Product Details

- Used for Evaluation of Resolution, Field Distortion, and Parfocal Stability
- Ideal for Reticle and Field Calibration Requirements
- Available on Float Glass, Fused Silica, Fused Silica with Fluorescent Backing, and [Opal](#).

Precision Ronchi Ruling Glass slides are excellent for evaluating resolution, field distortion, and parfocal stability, especially of microscopes. Many different Linepairs Per Millimeter (lp/mm) versions available.