

## 4.0 OD M22 x 0.75, Machine Vision Absorptive ND Filter



Stock #21-535 **2 In Stock**

MRP ₹16,748

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-9	₹16,748 each
Qty 10+	₹15,941 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Mounted Imaging Filter **Type:**

### Physical & Mechanical Properties

18.00 **Clear Aperture CA (mm):**

### Optical Properties

4.0 **Optical Density OD (Average):**

ND Filter Glass	<b>Substrate:</b> □
40-20	<b>Surface Quality:</b>
0.01	<b>Transmission (%):</b>
425 - 675	<b>Blocking Wavelength Range (nm):</b>

## Threading & Mounting

M22 x 0.75	<b>Filter Thread:</b>
5.2	<b>Mount Thickness (mm):</b>
7.0	<b>Mount Thickness Including Threads (mm):</b>

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 242:</b>
United States	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Product Details

- Multiple Mounting Sizes and Threads Available
- 40-20 Surface Quality
- Helps Minimize Pixel Saturation

Machine Vision Absorptive Neutral Density (ND) Filters are designed to evenly attenuate the intensity of light over a specific wavelength range reaching a camera's sensor. These neutral density filters are spectrally flat in the visible spectrum from 425 – 675nm, so there is little to no effect on color balance. As such, these filters can be used with both monochromatic and color cameras. Machine Vision Absorptive Neutral Density (ND) Filters include both male and female threads, allowing them to be stacked with other neutral density filters to achieve various optical densities. Featuring common machine vision threads from M22 up to M105, these neutral density filters can be easily integrated into a wide variety of systems.