

4.0 OD M58 x 0.75, Machine Vision Absorptive ND Filter



Stock #21-739

10 TO 12 DAYS

-

1

+

₹10,788.00

ADD TO CART

Qty 1-9
₹10,788.00
Qty 10+
₹10,275.00
Volume Pricing
Request Quote

Get Product Downloads

Optical Density OD (Average):

4.0

Clear Aperture CA (mm):

53.00

Filter Thread:

M58 x0.75

Substrate:

ND Filter Glass

Surface Quality: 40-20
Transmission (%): 0.01
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 425 - 675
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
