

TECHSPEC®

40mm Dia. High Performance Glass Linear Polarizer



Stock #66-182 10 TO 12 DAYS

-

1

+

₹19,053.00

ADD TO CART

Qty 1-5
₹19,053.00
Qty 6+
₹15,225.00
Volume Pricing
Request Quote

Get Product Downloads



Coating:
AR: R_{avg} <0.5% @ 400 - 700nm

Diameter (mm):
40.00

Extinction Ratio:
10,000:1

Substrate: ☐

Polymer Film between B270
Operating Temperature (°C): -25 to +65
Thickness (mm): 2.00
Thickness Tolerance (mm): ±0.2
Transmission (%): 25 (for random polarization)
Transmission Tolerance (%): ±2
Type: Linear Polarizer
Parallelism (arcmin): <4
Dimensional Tolerance (mm): +0.0/-0.2
Construction: Dichroic Polarizing Film between Glass
Wavelength Range (nm): 400 - 700
Surface Flatness (P-V): <1λ
Polarization Axis Mark (°): ±2

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View